


-?K
In: DC 24 V/6,85 A
Out: DC 24 V/6 A



+2V

1

ON

OFF

■

+1V

2

■

+0.5V

3

■

+1V

4

■

+1V

5

■

+0.5V

6

■

+0.2V

7

■

+0.2V

8

■

+0.1V

9

■

0.2/0.4A

10

■

CUT-IN_TRESHOLD

22,5V

END-OF-CHARGE_VOLTAGE

26,6V

CHARGING_CURRENT

0.4A

↙

1

ON

OFF

■

+320s

2

■

+160s

3

■

+80s

4

■

+40s

5

■

+20s

6

■

+10s

7

■

Unterbr.

8

■

On/Off

9

■

BUFFERING_TIME

MAX._TIME

BUFFERING_TIME

5s

DISCONNECTION

OFF

OPERATING_STATE_BATTERY

OFF

SIEMENS

SITOP DC-USV-MODUL 6A

MIT SERIELLER SCHNITTSTELLE

6EP19312DC31